


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	NOTES
1	50-00027	Connector, dc jack, 5.5x2.5xL17.4 mm, molding style	1	
2	30-00003	Wire, 2C BC, 24 AWG, UL2468, 300V, 80C, 3.6 mm, VW-1, PVC, 76A	1	
3	24-00004	Overmold, PVC, black	1	



Notes:
Functionally equivalent components may be substituted
Cable rated for 48 V, 4.5 A

Wiring diagram	
50-00027	Wire Color
Center	Black with stripe
Sleeve	Black

Revision:	Date:	Description:	Prepared:	Notes:	TENSILITY tel 1.541.323.3228 800 877.670.7118 fax 1.541.323.4202 web tensility.com		
A	6/27/2012	Initial release	Verified:				
			Dimensions are in millimeters.	Description:	Size:	Part number:	
			Tolerances:		A	10-01091	
			X: ± 0.5 mm	Cable, 1830 mm, 5.5x2.5 mm 50-00027 dc jack to stripped tinned, 24 AWG, 30-00003 wire	Scale:	1:1	Sheet 1 of 1
			X.X: ± 0.3 mm				
			X.XX: ± 0.05 mm				