

Specification Sheet

Part Number: 156-01726

Delivers high pull-out force for reliable performance, yet it's easy to install.

Reusable fastener can be extracted from threaded or nonthreaded holes using a 5/16" hex driver.

Heat-stabilized material provides excellent resistance to high temperatures.



Blind Hole Mount Outside Serrated Cable Tie for 1/4" Thread/Non-Thread Hole, 8", 50lb, PA66HS, Black, 500/bg

Article Number	156-01726
----------------	-----------

Type	T50RBHMB
------	----------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton Blind Hole Mount Cable Ties for threaded and nonthreaded holes offer an easy-to-use method for bundling and affixing cables. The two-piece design includes a heat-stabilized cable tie and formula-matched, 1/4" mount that features a low push-in force and aggressively resists pull out. Performs equally well in threaded or nonthreaded blind holes. Mount can slide along cable tie to adjust orientation if needed. Fastener can be removed from hole using a hex driver, ensuring reuse if desired.
---------------------	---

Short Description	Blind Hole Mount Outside Serrated Cable Tie for 1/4" Thread/Non-Thread Hole, 8", 50lb, PA66HS, Black, 500/bg
-------------------	--

Global Part Name	T50RBHMB-PA66HS-BK
------------------	--------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	8.0
---------------------	-----

Length L (Metric)	203.2
-------------------	-------

Fixation Method	Blind Plug
-----------------	------------

Identification Plate Position	none
-------------------------------	------

Width W (Imperial)	0.31
--------------------	------

Width W (Metric)	7.8
------------------	-----

Bundle Diameter Min (Imperial)	0.1
--------------------------------	-----

Bundle Diameter Min (Metric)	2.5
------------------------------	-----

Bundle Diameter Max (Imperial)	1.97
--------------------------------	------

Bundle Diameter Max (Metric)	50.0
------------------------------	------

Height H (Imperial)	0.736
---------------------	-------

Height H (Metric)	18.7
-------------------	------

Diameter D (Imperial)	0.25
-----------------------	------

Diameter D (Metric)	6.35
Mounting Hole Diameter D (Imperial)	0.246 - 0.253 "
Mounting Hole Diameter D (Metric)	6.25 - 6.45 mm
Mounting Hole Diameter D Min (Imperial)	0.25
Mounting Hole Diameter D Max (Imperial)	0.25
Mounting Hole Diameter D Max (Metric)	6.45
Disc Diameter (Metric)	10.9
Disc Diameter (Imperial)	0.43
Material	Polyamide 6.6 heat stabilized (PA66HS)
Foot Part Material	PA66HS
Material Shortcut	PA66HS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 V-2
Halogen Free	No
UV Resistant (Yes/No)	No

Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)