



Part Number : [1064810112](#)

Product Description : LGX Cassette, 24 LC/PC-to-2
Male MTP/PC, Aqua

Series Number : 106406

Status : Active

Product Category : Fiber Optic Adapters




Documents and Resources

Drawings

[1064810112_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per ED/71/2019 (16 July 2019)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Fiber Optic Adapters
Series	106406
Description	LGX Cassette, 24 LC/PC-to-2 Male MTP/PC, Aqua
Component Type	Cassette
Product Name	Fiber Enclosures and Cassettes
Type	LGX
UPC	191128975100

Electrical

Shielded	No
Shield Type	N/A

Physical

Alignment Sleeve	Zirconia
Angled Physical Contact (APC)	No
Color - Resin	Aqua
Gender	Male
Height	28.80mm
Material - Housing	Plastic
Mounting Style	Flange
Orientation	Straight
Panel Mount	N/A
Ports	24
Shutter	No

Mates With / Use With

Use with Part(s)

Description	Part Number
Rack-Mount Fiber Enclosure, 1RU, 3 LGX Cassette / 72-Port Capacity	<u>1064800100</u>
Rack-Mount Fiber Enclosure, 2RU, 6 LGX Cassette / 144-Port Capacity	<u>1064800101</u>
Rack-Mount Fiber Enclosure, 3RU, 12 LGX Cassette / 288-Port Capacity	<u>1064800102</u>
Rack-Mount Fiber Enclosure, 4RU, 12 LGX Cassette / 288-Port Capacity	<u>1064800103</u>

This document was generated on May 27, 2026