



Part Number : [39000376](#)


Product Description : KK 254 Crimp Terminal, Female, 28-22 AWG, 0.38µm Selective Gold (Au) Plated Brass, Reel

Series Number : 2759

Status : Active

Product Category : Crimp Terminals

Engineering Part Number : 2759G



Documents and Resources

Drawings

[039000376 sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-2759-003-001.pdf](#)

[PS-2759-004-001.pdf](#)


[PS-5045-003-001.pdf](#)

[PS-5045-004-001.pdf](#)

[50510002-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	2759
Description	KK 254 Crimp Terminal, Female, 28-22 AWG, 0.38µm Selective Gold (Au) Plated Brass, Reel
Application	Wire-to-Board
Product Name	KK 254
UPC	800753336483

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	0.064/g
Packaging Type	Reel
Plating min - Mating	0.380µm
Plating min - Termination	0.050µm
Termination Interface Style	Crimp or Compression

Wire Insulation Diameter	1.20-1.70mm max.
Wire Size (AWG)	22, 24, 26, 28
Wire Size mm ²	N/A

Solder Process Data

Max-Duration	5
Lead-Free Process Capability	WAVE
Max-Cycle	1
Max-Temp	260

Mates With / Use With

Use with Part(s)

Description	Part Number
KK 254 Single Row Crimp Housings	<u>2695</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for KK 2.54mm Terminals, 30-22 AWG	<u>11030022</u>
Insertion Tool for KK 2.54mm Terminals, 30-22 AWG	<u>638120000</u>
Mini-Mac Applicator for KK and Cat Ear Terminals for 30-22 AWG Wire with Insulation Diameter 1.09-1.57mm and 28-22 AWG Wire with Insulation Diameter 1.20-1.70mm	<u>638882000</u>
Mini-Mac Applicator for KK and Cat Ear Terminals for 30-22 AWG Wire with Insulation Diameter 0.96-1.20mm	<u>638882100</u>