Data Sheet | Item Number: 216-267


Ferrule; Sleeve for 4 mm² / AWG 12; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray

https://www.wago.com/216-267



Color: gray

Similar to illustration



Dimensions in mm

Connection Data	
Metric cross-section of the ferrule	4 mm²
Strip length	14 … 15 mm / 0.55 … 0.59 inches
Cross-section (AWG) of ferrule	12 AWG

Physical data	
Total length	20 mm
Wall thickness of crimp sleeve	0.2 mm
Wall thickness (plastic collar)	0.3 mm
Crimp length (length of sleeve)	12 mm
Inner diameter of plastic collar	4.8 mm
Diameter crimp sleeve inside	2.8 mm

Mechanical data	
Plastic collar	Standard collar
Suitable	2004 to 2006 Series

Material data	
Color	gray
Fire load	0.001 MJ
Weight	0.2 g

Downloaded from Arrow.com.

Commercial data

Product Group	2 (Terminal Block Accessories)
PU (SPU)	500 (100) pcs
Packaging type	Bag
Country of origin	DE
GTIN	4055143654739
Customs tariff number	85369010000

Product Classification

UNSPSC	39121405
eCl@ss 10.0	27-40-02-01
eCl@ss 9.0	27-40-02-01
ETIM 9.0	EC000005
ETIM 10.0	EC000005
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search


Environmental Product Compliance 216-267

Documentation

Bid Text

216-267	19.02.2019	xml 2.80 KB	
216-267	11.09.2017	doc 24.00 KB	

Installation Notes



A perfect gas-tight crimp – both electrically and mechanically reliable

Downloaded from Arrow.com.