



Part Number : [1301090017](#)

Product Description : Pro-Yellow Nylon 100W Hand Lamp with Switch, Molded Grips and Hide Away Guard, Cord Type 18/3 SJTW, Cord Length 6.10m (20.0')

Series Number : 130109

Status : Obsolete

Product Category : Lamps and Lights

Engineering Number : WT3C-20



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Lamps and Lights
Series	130109
Description	Pro-Yellow Nylon 100W Hand Lamp with Switch, Molded Grips and Hide Away Guard, Cord Type 18/3 SJTW, Cord Length 6.10m (20.0')
NEMA Configuration	NEMA 5-15
Product Name	Pro-Yellow
Type	Hand Lamps
UPC	78678850114

Agency

UL	E59049
----	--------

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Incandescent
Cord Length - Primary	6.10m (20.0')
Cord Length - Secondary	N/A
Cord Type - Primary	18/3 SJTW
Depth	N/A
Duty	General
Guard Included	Yes
Guard Type	Hide Away
Height	N/A
Lamp Type	A21
Length	N/A

Material - Guard	Polypropylene
Mounting Style	Hand Held
Outlet	None
Packaging Type	Carton

This document was generated on Sep 23, 2025

Obsolete