




- 注:
- △ 0.65tタブと嵌合。
 - 2. 嵌合相手タブ型番 172777, 172778
 - 3. 製品規格 No.108-S165, 5166.
 - 4. 取付適用規格 No.114-5071.
 - 5. 相手ハウジング型番 172500 他。
 - △ 逆巻きリール。

- NOTES;
- △ MATE WITH 0.65t TAB.
 - 2. MATE TAB P/N 172777, 172778.
 - 3. PRODUCT SPEC. No. 108-5165, 5166.
 - 4. APPLICATION SPEC. No. 114-5071.
 - 5. PLUG HSG P/N 172500 ETC.
 - △ REVERSE REEL

172774-5	銅メッキ済 (PRE-TIN)	KLF-5	△ 1-172773-5	7
172774-1	銅メッキ済 (PRE-TIN)	黄銅 (BRASS)	△ 1-172773-1	6
172774-6	鍍金メッキ (SELECTIVE GOLD) △	黄銅 (PHOS BRO)	172773-6	5
172774-5	銅メッキ済 (PRE-TIN)	KLF-5	172773-5	4
172774-4	銅メッキ済 (PRE-TIN)	黄銅 (PHOS BRO)	172773-4	3
172774-2	鍍金メッキ (SELECTIVE GOLD) △	黄銅 (BRASS)	172773-2	2
172774-1	銅メッキ済 (PRE-TIN)	黄銅 (BRASS)	172773-1	1
パラ状端子型番 (P.N.O.)	仕上 (FINISHED)	材料 (MATERIAL)	型番 (P/N)	項番 (ID)

Copyright ©1982 AMP (Japan), LTD. ALL RIGHTS RESERVED.				Copyright ©1982 AMP (Japan), LTD. ALL RIGHTS RESERVED.			
WIRE RANGE 0.5-2.27mm ² (AMS#20-#14)				INSULATION DIA 2.1~3.4 mm			
MATERIAL 表参照 SEE TABLE				FINISH 表参照 SEE TABLE			
G L/P NO -S0804E J-1804				F REDRAWN W/CHANGE J-10628			
LTR REVISION RECORD				ON CHK DATE			
Copyright ©1982 AMP (Japan), LTD. ALL RIGHTS RESERVED.				Copyright ©1982 AMP (Japan), LTD. ALL RIGHTS RESERVED.			
WIRE RANGE 0.5-2.27mm ² (AMS#20-#14)				INSULATION DIA 2.1~3.4 mm			
MATERIAL 表参照 SEE TABLE				FINISH 表参照 SEE TABLE			
G L/P NO -S0804E J-1804				F REDRAWN W/CHANGE J-10628			
LTR REVISION RECORD				ON CHK DATE			

AMP AMP (JAPAN), LTD. Tokyo, Japan

リセプタクル コンタクト マルチラインターロックコネクタ (MIC) マークII			
RECEPTACLE MIC MK II			
GENERAL TOLERANCE		LOC NUMBER	
0-circ 10 : ±0.2		B J C-172773	
10-circ 30 : ±0.25		SCALE 5-1	
30-circ 100 : ±0.3		REV. G	
ANGLES : ±3°		SHEET 1 OF 1	

CUSTOMER DRAWING