






REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL	MAR 31/16	LCHAN
B	Correct gold plating	JUN 15/16	LCHAN
C	REVISE THE NOTES	FEB 24/17	LCHAN




RECOMMENDED PANEL CUTOUT

MATERIALS:
PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC
FLAMMABILITY RATING UL94V-0, COLOUR BLACK.
CONTACT: PHOSPHOR BRONZE.
CONTACT PLATING: SELECTIVE GOLD PLATING ON MATING SURFACES.
SEE PART NO. FOR THICKNESS.
50u" [1.27 MICRONS] MIN, NICKEL UNDERPLATE.
100u" [2.54 MICRONS] MIN, MATTE-TIN ON CONTACT TAILS.

AMPHENOL PART NUMBER: RJE1J-188-0X10


- Gold plating:
- 0. gold plating (1~3u")
 - 1. 6u" gold plating
 - 2. 15u" gold plating
 - 3. 30u" gold plating
 - 4. 50u" gold plating



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)
PCB THICKNESS: 1.57MM
TOLERANCE: +/-0.05MM

UNLESS SPECIFIED OTHERWISE		DRAWN	FRANK W	MAR31/16	Amphenol Canada Corp.	
PRIMARY UNITS	MILLIMETERS	CHECKED	LCHAN	MAR31/16		
SECONDARY		M.E. APP'D			MODULAR JACK, SINGLE PORT, VERTICAL MOUNT, 8P8C, WITHOUT SHIELD. TRAY PACKAGING - RoHS COMPLIANT	
REFERENCE IN PARENTHESES		QA APP'D				
GENERAL TOLERANCES		DWG APPR.			P-RJE1J-188-0X10	
1 DECIMAL PLACE	± 0.38	ENG. REL. NO.				
2 DECIMAL PLACES	± 0.20	REF.			REV C	
3 DECIMAL PLACES	± 0.10	THIRD ANGLE PROJECTION				
ANGULAR DEGREES	± 10 °	DO NOT SCALE DRAWING			CODE ID NO. 03554 DWG SIZE: X SCALE: 40 SHEET 1 OF 2	

REVISIONS			
SYM	ZONE	ECN, ERN NO.	DATE
A		PROPOSAL	MAR31/16
B		Correct gold plating	JUN15/16
C		REVISE THE NOTES	FEB 24/17



12 TRAY PER CARTON

LABEL

SEAL THE CARTON

PACKAGING NOTES:

- 1. 110PCS CONNECTORS PER TRAY
- 2. 12 TRAY PER CARTON (1320 PCS CONNECTORS PER CARTON)

DRAWN	FRANK.W	DATE	MAR31/16
DESIGNED			
CHECKED	L.CHAN	MAR31/16	
I. E. APPRD.			
Q. A. APPRD.			
DWG. APPRD.			
ENG. REL. NO.			
REF.			
DIMENSIONS ARE IN	CODE ID. NO.		
INCHES [mm]	03554		

Amphenol Canada Corp.			
TITLE MODULAR JACK, SINGLE PORT, VERTICALACAL MOUNT, 8P8C, WITHOUT SHIELD. TRAY PACKAGING – RoHS COMPLIANT			
DWG	DRAWING NO.	REV.	
	P-RJE1J-188-0X10	C	
SCALE	WT.	SURF.	SHEET 2 OF 2