Part Number : 732764050
Product Description : N Plug, Straight, Clamp, RG-213/U Cable, Brass Body, Nickel (Ni) Plated, Bag, 50 Ohms
Series Number : 73276
Status : Active
Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

732764050_sd.pdf

Specifications

AS-73597-039-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73276
Description	N Plug, Straight, Clamp, RG-213/U Cable, Brass Body, Nickel (Ni) Plated, Bag, 50 Ohms
Application	RF
Product Name	N
Style	Cable
Type	Medium
UPC	883906905347

Electrical

Frequency	11 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 1000 Vrms@Sea Level

Physical

Cable Attachment	Clamp
Gender	Plug
Keying to Mating Part	N/A
Net Weight	48.783/g
Orientation	Straight
Packaging Type	Bag
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A

Downloaded from Arrow.com.

Reverse Polar	No
Wire/Cable Type	RG-213, RG-214, RG-225

Downloaded from Arrow.com.