




NOTES:

- 1. BRAIDED STRAP IS #4 AWG STRANDED COPPER, TIN PLATED
FERRULES ARE TIN PLATED COPPER.
- 2. INSULATION:
MATERIAL - POLYOLEFIN SLEEVE
TEMPERATURE RATING - 135° C
COLOR - INDUSTRY STANDARD YELLOW/GREEN
- 3. DIMENSIONS IN PARENTHESIS ARE MILLIMETERS.
- 4. PARTS ARE UL LISTED FOR BONDING APPLICATIONS ONLY.



PANDUIT PART NUMBER	BRAIDED STRAP SIZE	INSULATION (SEE NOTE 2)	NO. OF BRAIDS IN FERRULE	DIMENSIONS - IN [mm] + .02 [0.5]						
				L	D	W	C	T	H DIA	FERRULE LENGTH
BS100445	4 AWG	YES	1	4.00 [101.6]	3.00 [76.2]	1.06 [27.0]	0.50 [12.7]	0.13 [3.3]	0.41 [10.3]	1.00 [25.4]
BS100645	4 AWG	YES	1	6.00 [152.4]	5.00 [127.0]	1.06 [27.0]	0.50 [12.7]	0.13 [3.3]	0.41 [10.3]	1.00 [25.4]
BS100845	4 AWG	YES	1	8.00 [203.2]	7.00 [177.8]	1.06 [27.0]	0.50 [12.7]	0.13 [3.3]	0.41 [10.3]	1.00 [25.4]
BS101245	4 AWG	YES	1	12.00 [304.8]	11.00 [279.4]	1.06 [27.0]	0.50 [12.7]	0.13 [3.3]	0.41 [10.3]	1.00 [25.4]
BS100445U	4 AWG	NO	1	4.00 [101.6]	3.00 [76.2]	1.06 [27.0]	0.50 [12.7]	0.13 [3.3]	0.41 [10.3]	1.00 [25.4]
BS100645U	4 AWG	NO	1	6.00 [152.4]	5.00 [127.0]	1.06 [27.0]	0.50 [12.7]	0.13 [3.3]	0.41 [10.3]	1.00 [25.4]
BS100845U	4 AWG	NO	1	8.00 [203.2]	7.00 [177.8]	1.06 [27.0]	0.50 [12.7]	0.13 [3.3]	0.41 [10.3]	1.00 [25.4]
BS101245U	4 AWG	NO	1	12.00 [304.8]	11.00 [279.4]	1.06 [27.0]	0.50 [12.7]	0.13 [3.3]	0.41 [10.3]	1.00 [25.4]

							TITLE
							ONE-HOLE BRAIDED BONDING STRAPS
							CUSTOMER DRAWING
						ITEM REVISION NAME	N11002BE/06
						DATASET FILE NAME	N11002BE-DC/06.SLDDRW
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	MATERIAL
						.X ± .XX ± .02 [0.5]	.XXX ± ANGLES ±
							THIRD ANGLE PROJECTION
00	4/18	JHNU	JHNU	RGB	ADDED ± .02 [0.5] TOLERANCE REVISED TITLE BLOCK	033692	DRAWING NUMBER
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	C41744
							SHEET 1 OF 1
							SIZE B