Quick Links
RoHS/LF P/N Search

Documentation
Customer drawing search
Free search

Services
Distributor list

54200212

54200212 : 2 Way 2.8 mm APEX coupling Female housing



Customer drawing

ACTIVE

Add to Favorites
Print Datasheet

FCI Brings You More
Contact our sales/technical support
Sample request

Specifications | Download document | Mating Half

General | Mechanical | Physical | Terminal 1 Type | Environmental | Other Features

General	
Application	Wire to Wire Component-to-Wire
Ways	2
Coding version	A
Product Type	Housing
Coding	Yes
Features	Mechanical polarization Circumferential interface seal Terminal position assurance (T.P.A.) Connector position assurance (C.P.A.) Rear sealing ensured by a pre-mounted grommet Fastening clip available
Hybrid	No
Main Terminal family	APEX
Main Terminal size	2.8 mm
Sealed	Yes
Terminal Size	2.8
Mechanical	
Connector mating force	< 75N
Physical	
Color	Light Green
Material	PA
Temperature (Range)	-40°C to +125°C
Terminal 1 Type	
Terminal type 1	APEX Female 2.8 mm Terminal
Ways for Terminal Type 1	2
Contact insertion force for Terminal Type 1	< 15N
Contact Pitch for Terminal Type 1	5.25 mm
Retention force (Contact) for Terminal Type 1	> 90N
Environmental	
IMDS	Yes
Other Features	
Market	Passenger Vehicles
Type	Female
Part Situation	Active
Disclaimer	For more information, please contact your local sales office. Displayed data is for information purposes only The supply of some products might be limited to some customers

Downloaded from Arrow.com.