


SKINDICHT® BLK-GL-M

SKINDICHT® BLK-GL-M, glass fibre-reinforced polyamide blind plugs with high stability for closing pre-threaded holes



Robust



Reliability



Waterproof

Benefits

For closing pre-threaded holes
High stability due to glass fibre reinforcement

Application range

Control cabinet manufacturing
Distribution box
Junction boxes

Product features

Assembling with screwdriver

Product Make-up

Metric connection thread acc. to DIN EN 60423
Basis for technical information DIN IEC 62444

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000032

ETIM 5.0 Class-Description: Plug for cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000032

ETIM 6.0 Class-Description: Plug for cable screw gland

Last Update (11.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINDICHT® BLK-GL-M

Certifications:	UL pending
Colour delivered:	Silver grey (RAL 7001) Light grey (RAL 7035) Black (RAL 9005)
Material:	Polyamide, glass fibre-reinforced O-Ring: NBR
Protection rating:	IP 54 IP 68 (with O-ring)
Temperature range:	With O-ring: -20 °C to +100 °C Without O-ring: -40 °C to +100 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® BLK-GL-M

Article number	Article designation / size	Overall length C mm	Thread length D mm	Outer Ø (mm)	Pieces / PU
SKINDICHT® BLK-GL-M silver-grey					
52006101	M 12 x 1,5	8.7	7	15.0	100
52006111	M 16 x 1,5	9.8	7	20.0	100
52006121	M 20 x 1,5	10.3	7	24.0	100
52006131	M 25 x 1,5	11.5	8	30.0	100
52006141	M 32 x 1,5	12.0	8	37.0	50
52006151	M 40 x 1,5	13.0	8	46.0	25
52006161	M 50 x 1,5	15.0	10	56.0	25
52006171	M 63 x 1,5	17.0	12	70.0	25
SKINDICHT® BLK-GL-M light grey					
52006100	M 12 x 1,5	8.7	7	15.0	100
52006110	M 16 x 1,5	9.8	7	20.0	100
52006120	M 20 x 1,5	10.3	7	24.0	100
52006130	M 25 x 1,5	11.5	8	30.0	100
52006140	M 32 x 1,5	12.0	8	37.0	50
52006150	M 40 x 1,5	13.0	8	46.0	25
52006160	M 50 x 1,5	15.0	10	56.0	25
52006170	M 63 x 1,5	17.0	12	70.0	25
SKINDICHT® BLK-GL-M black					
52006103	M 12 x 1,5	8.7	7	15.0	100
52006113	M 16 x 1,5	9.8	7	20.0	100
52006123	M 20 x 1,5	10.3	7	24.0	100
52006133	M 25 x 1,5	11.5	8	30.0	100
52006143	M 32 x 1,5	12.0	8	37.0	50
52006153	M 40 x 1,5	13.0	8	46.0	25
52006163	M 50 x 1,5	15.0	10	56.0	25
52006173	M 63 x 1,5	17.0	12	70.0	25
SKINDICHT® BLK-GL-M silver-grey mounted with O-ring					
52006109	M 12 x 1,5	8.7	7	15.0	100
52006119	M 16 x 1,5	9.8	7	20.0	100
52006129	M 20 x 1,5	10.3	7	24.0	100
52006139	M 25 x 1,5	11.5	8	30.0	100
52006149	M 32 x 1,5	12.0	8	37.0	50
52006159	M 40 x 1,5	13.0	8	46.0	25
52006169	M 50 x 1,5	15.0	10	56.0	25

Last Update (11.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

SKINDICHT® BLK-GL-M

Article number	Article designation / size	Overall length C mm	Thread length D mm	Outer Ø (mm)	Pieces / PU
52006179	M 63 x 1,5	17.0	12	70.0	25
SKINDICHT® BLK-GL-M light grey mounted with O-ring					
52006107	M 12 x 1,5	8.7	7	15.0	100
52006117	M 16 x 1,5	9.8	7	20.0	100
52006127	M 20 x 1,5	10.3	7	24.0	100
52006137	M 25 x 1,5	11.5	8	30.0	100
52006147	M 32 x 1,5	12.0	8	37.0	50
52006157	M 40 x 1,5	13.0	8	46.0	25
52006167	M 50 x 1,5	15.0	10	56.0	25
52006177	M 63 x 1,5	17.0	12	70.0	25
SKINDICHT® BLK-GL-M black mounted with O-ring					
52006106	M 12 x 1,5	8.7	7	15.0	100
52006116	M 16 x 1,5	9.8	7	20.0	100
52006126	M 20 x 1,5	10.3	7	24.0	100
52006136	M 25 x 1,5	11.5	8	30.0	100
52006146	M 32 x 1,5	12.0	8	37.0	50
52006156	M 40 x 1,5	13.0	8	46.0	25
52006166	M 50 x 1,5	15.0	10	56.0	25
52006176	M 63 x 1,5	17.0	12	70.0	25

Last Update (11.12.2022)
 ©2022 Lapp Group - Technical changes reserved
 Product Management www.lappkabel.de
 You can find the current technical data in the corresponding data sheet.
 PN 0456 / 02_03.16