HellermannTyton

Technical data sheet

Article number:
133-02773 CCAH8.5X16PT4-5

Material	Polypropylene (PP)
Colour	Black (BK)

CE Certification	No
Fixation Method	arrowhead
for Hole Ø (FH)	8.5 - 16.0 mm
Height (H)	21.65 mm
Length (L)	27.07 mm
Operating Temperature	-40 °C to +115 °C
Package Content	2500 Carton
Package Content packed in	carton
Panel Thickness	4.0 - 5.0 mm
Panel Thickness max.	5.0 mm
Panel Thickness min.	4.0 mm
ROHS compliant	Yes
UV-Stabilised	Yes
Width (W)	21.36 mm

RoHS

created on 8. May 2026, 4:29 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.