



BU-00000-*
Part # color

* 0 - Black 5 - Green
2 - Red 6 - Blue
4 - Yellow 9 - White

TEST LEADS

1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 Page 2



Enlarge

BU-1031-A-00-*

"Mini-Plunger Clip" To Insulated Mini-Alligator Clip

- "Mini-Plunger Clip" (No. 201) spring-loaded hook.
- One-piece beryllium copper conductor.
- 30BL Insulated Mini-Alligator Clip.
- Plated steel with 3/16" (4.7 mm) jaw opening.
- Hook-up Wire: Stranded #20 AWG (41/36) tinned copper with 105°C PVC insulation.
- [Product Data Sheet](#)
- [Send us your questions about this product](#)

BU-1080-E-00-*

"Mini-Micro-Plunger Clip" To 0.025" (0.6 mm) Square Pin Receptacle

- Mini-Micro-Plunger (No. 201) speeds terminal connections.
- Pin Receptacle: 0.025" (0.6 mm) copper-nickel-tin alloy 725 with 0.000030 (0.00076 mm): gold contact plating.
- Mates to 0.025" x 0.025" (0.6 mm x 0.6 mm) square pin.
- ABS Housing.
- #22 AWG wire (19/34) tinned copper with 105°C PVC insulation.
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



Enlarge

BU-1120-A-00

"Mini-Plunger To Stackable Banana Plug"

- Three Plunger sizes and five lengths.
- Spring-loaded, beryllium copper conductor firmly but gently attaches to leads and terminals.
- #20 AWG wire (41/36) tinned copper with 105°C PVC insulation.
- [Product Data Sheet & Compatibility Info.](#)
- [Send us your questions about this product](#)

BU-1414-E-00-*

"Mini-Micro-Plunger" On Both Ends

- No. 202 spring-loaded beryllium copper plunger hook.
- Safety shrouded four-leaf banana plug with nickel-silver plating.
- Stainless steel compression spring.
- Attaches to 0.025" (.6mm) dia. and smaller component leads.
- #22 AWG wire (41/36) tinned copper with 105°C PVC insulation.
- [Product Data Sheet & Compatibility Info.](#)
- [Send us your questions about this product](#)



[Contents](#)|[Next](#)
[Home](#)|[Insulated BNCs](#)|[Clips & Insulators](#)|[Insulated Test Accessories](#)
[Accessories & Probes](#)|[Kits](#)|[Cross Reference](#)

©1999-2000 Mueller Electric Company. All rights reserved.
Problems with the site should be reported to the [webmaster](#).