



Part Number : [1301040086](#)
Product Description : Haztex High Output LED
Hand Lamp, Hazardous Duty, 20W, 16/3 SOOW Cord
Type, Cord Length 7.62m (25.0')
Series Number : 130104
Status : Active
Product Category : Lamps and Lights
Engineering Number : 61450A163



Documents & Resources

Drawings

[1301040086 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130104
Description	Haztex High Output LED Hand Lamp, Hazardous Duty, 20W, 16/3 SOOW Cord Type, Cord Length 7.62m (25.0')
Comments	E30252 (cULus): Class I, Division I, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust)
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Product Name	Haztex
Type	Hand Lamps
UPC	78172547861

Agency

UL	E30252
----	--------

Electrical

Lamp Wattage - Maximum	20W
Lumens	750
On/Off Switch	No
Voltage (Fixture) - Maximum	120V AC

Physical

Bulb Type	LED - 5000K
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A

Cord Type - Primary	16/3 SOOW
Depth	127.00mm (5.000")
Duty	Hazardous
Guard Included	Yes
Guard Type	Cast Aluminum
Height	N/A
Lamp Type	LED
Length	376.00mm (14.800")
Material - Globe	Tempered Soda-Lime Glass
Material - Guard	Cast Aluminum
Mounting Style	Hand Held
Net Weight	315.000/g
Outlet	None
Packaging Type	Carton

This document was generated on Sep 23, 2025