# Laptop Power Adapter Cord, C14 to C5 Adapter - 7A/125V or 2.5A/250V, 18 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: **P014-006**









Laptop power cord adapter connects your notebook or laptop with a 3-slot C6 power inlet to an AC outlet.

## Features

**Laptop Power Adapter Cord Connects Notebook Computers to an AC Outlet**This C5 to C14 power cord is designed for connecting a notebook computer, laptop or other device with a three-slot C6 inlet to a UPS system, PDU or other C13 connector. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

## Highlights

- Recommended for powering notebook computers and laptops with C6 inlets
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing laptop adapter power cable

## Applications

- Connect a laptop or notebook computer to a PDU up to 6-ft. (1.83 m) away in your workstation
- Extend an existing power connection up to 6-ft. (1.83 m) to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing laptop power cord

## Package Includes

- P014-006 Laptop Power Adapter Cord, C14 to C5 Adapter - 6-ft. (1.83 m), Black

# Specifications

| | |
|---|---|
| **OVERVIEW** | |
| UPC Code | 037332098757 |
| Product Type | Computer Power Adapter |
| Device Compatibility | Laptop; Computer; UPS; PDU |
| Country/Region | North America |
| **INPUT** | |
| Maximum Input Amps | 7 |
| Voltage Compatibility (VAC) | 250 |
| **CONNECTIONS** | |
| Side A - Connector 1 | IEC-320-C14 |
| Side B - Connector 1 | IEC-320-C5 |
| Connector Style | Straight |



Downloaded from Arrow.com.

| | |
|---|---|
| **PHYSICAL** | |
| Color | Black |
| Plug Color | Black |
| Cable Jacket Color | Black |
| Connector Color | Black |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | VW-1 |
| Power Cord Jacket Type | SJT |
| Cable Outer Diameter (OD) | 7.8mm |
| Number of Conductors | 3 |
| Wire Gauge (AWG) | 18 |
| Wire Gauge (OD - $mm^2$) | 0.82 |
| Power Cord Color | Black |
| Cable Length (ft.) | 6 |
| Cable Length (m) | 1.83 |
| Shipping Dimensions (hwd / in.) | 12.80 x 8.90 x 0.50 |
| Shipping Dimensions (hwd / cm) | 32.51 x 22.61 x 1.27 |
| Shipping Weight (lbs.) | 0.46 |
| Shipping Weight (kg) | 0.21 |
| Unit Dimensions (hwd / in.) | 12.800 x 8.900 x 0.500 |
| **ENVIRONMENTAL** | |
| Operating Temperature Range | -4° to 140°F (-20° to 60°C) |
| Storage Temperature Range | -4° to 140°F (-20° to 60°C) |
| Operating Humidity Range | 10% to 65% RH |
| Storage Humidity Range | 10% to 65% RH |
| **FEATURES & SPECIFICATIONS** | |
| Antibacterial | No |
| Angled Plug | No |
| High Voltage | Yes |
| Locking Plug | No |
| Coiled Power Cord | No |
| Locking Power Cord | No |
| Locking | No |



Downloaded from Arrow.com.

| STANDARDS & COMPLIANCE | |
|---|---|
| Product Certifications | cUL Listed; UL Listed |
| Product Compliance | RoHS |
| **WARRANTY & SUPPORT** | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.



Downloaded from Arrow.com.