

# Product data sheet

Specifications



## APC Replacement Battery Cartridge #133 with 2 Year Warranty

APCRBC133

### Overview

Lead time	Usually in Stock
-----------	------------------

### Main

Number of cables	1
Battery type	Lead-acid battery
Provided equipment	All required connectors Battery recycling guide Metallic battery tray or enclosure Reusable packaging Installation guide

### Physical

Colour	Black
Height	8.3 cm
Width	21.6 cm
Depth	34.3 cm
Net weight	11.96 kg
Mounting mode	Not rack-mountable
USB compatible	No

### Environmental

Ambient air temperature for operation	0...40 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m
Storage Relative Humidity	0...95 %

### Batteries & Runtime

Number of battery free slots	0
Number of battery filled slots	0

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Device mounting	Enclosed battery cartridge
Number of battery replacement quantity	1
<b>Packing Units</b>	
Package 1 Weight	12.6 kg
Package 1 Height	15.2 cm
Package 1 width	36.8 cm
Package 1 Length	49.5 cm
Number of Units in Package 3	20
<b>Offer Sustainability</b>	
Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
Take-back	Take-back program available
<b>Contractual warranty</b>	
Warranty	2 years repair or replace