



Pushing Performance
Since 1945

Han CGM-M M12x1,5 D. 3-6,5mm



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 5026
Specification	Han CGM-M M12x1,5 D. 3-6,5mm
HARTING eCatalogue	https://harting.com/19000005026

Identification

Category	Accessories
Series of hoods/housings	Han® CGM-M
Type of accessory	Cable gland

Technical characteristics

Wrench size	14
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M12
Clamping range	3 ... 6.5 mm
Width across corners	15.5 mm

Material properties

Material (cable glands)	Brass
Material (seal)	NBR
Material (clamping ring)	Polyamide (PA)
Surface (accessories)	Nickel plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol Lead
ECHA SCIP number	4f201c26-3e7e-4d14-b05e-d8c11d623635
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	10
Net weight	11.137 g
Country of origin	Germany
European customs tariff number	84849000
GTIN	5713140193017
eCl@ss	27140801 Screwed cable gland (electrical)
ETIM	EC000441
UNSPSC 24.0	39121431