
22759/32-26-5 Product Details



22759/32-26-5

TE Internal Number: 982620-000

Active

Spec 44, Spec 55 and Spec RCW Wire and Cable

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Cable Type = Spec 55
- Wire Source = United States
- Cable Style = Primary
- Wire Size (AWG/CM) = 26 AWG
- Voltage Rating = 600 VAC

View all Features

Add to My Part List | Request Sample | Find Similar Products | Buy Product

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Documentation & Additional Information

Product Drawings:
- Wire, Radiation-Crosslinked, Modified, ETFE-Insulate... (PDF, English)

Catalog Pages/Data Sheets:
- None Available

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- None Available

CAD Files:
- None Available

List all Documents

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Cable Type = Spec 55
- Cable Style = Primary
- Number of Conductors = 1

Electrical Characteristics:
- Voltage Rating (VAC) = 600

Body Features:
- Wire Size (AWG/CM) = 26 AWG
- Conductor Type = Tin-Plated Copper
- Wire Color = Green
- Nominal Outside Diameter (mm [in]) = 0.81 [0.032]
- Wire Diameter (mm [in]) = 0.81 [0.032]
- Conductor O.D. (mm [in]) = 0.50 [0.020]

Industry Standards:
- Government/Industry Qualification = Yes
- Government/Industry Part Number = M22759/32-26-5
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:
- Temperature Range (°C) = -65 – +150
- Wire Size - Details = 26 AWG 0.15 mm², 0.00024 in², 19 x 38 AWG

Operation/Application:
- Application = General Purpose - Lightweight

Packaging Features:
- Wire Source = United States

Other:
- Brand = Raychem

© 2012 Tyco Electronics Corporation, a TE Connectivity Ltd. company. All Rights Reserved | Privacy Policy

Provide Website Feedback

Downloaded from Arrow.com.