
Part Number : 2034560003
Product Description : Mirror Mezz Hermaphroditic Connector, 5.50mm Connector Height, BGA-Attach Mounting, 7 Pair, 11 Row, 699 Circuits, 0.76µm Gold (Au) Plating, without Pegs
Series Number : 203456
Status : Active
Product Category : Board-to-Board Connectors



Documents and Resources

Drawings

2034560003_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

2043581506EE-000.pdf

2043581506SP-000.zip

Specifications

2028280001-AS-000.pdf

2028280001-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 34; 33; 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

Downloaded from Arrow.com.

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	203456
Description	Mirror Mezz Hermaphroditic Connector, 5.50mm Connector Height, BGA-Attach Mounting, 7 Pair, 11 Row, 699 Circuits, 0.76µm Gold (Au) Plating, without Pegs
Application	Board-to-Board, Mezzanine
Component Type	Plug
Product Name	Mirror Mezz
UPC	191128393010

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	0.75A (1 Oz Cu Trace), 1.2A (2 Oz Cu Trace)
Voltage - Maximum	30V AC (RMS)/DC

Downloaded from Arrow.com.

Physical

Breakaway	No
Circuits (Loaded)	699
Circuits (maximum)	699
Color - Resin	Black
Durability (mating cycles max)	100
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	No
Lock to Mating Part	No
Mated Height	11.00mm
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	11.343/g
Number of Rows	11
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PCB Retention	Yes
Pitch - Mating Interface	1.50mm, 4.00mm
Plating min - Mating	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Unshrouded
Stackable	Yes
Temperature Range - Operating	-55° to +105°C
Termination Interface Style	BGA Solder

Solder Process Data

Max-Duration	20
Lead-Free Process Capability	REFLOW

Downloaded from Arrow.com.

Max-Cycle	1
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mirror Mezz Hermaphroditic Connector, 2.50mm Connector Height, BGA-Attach Mounting, 7 Pair, 11 Row, 699 Circuits, 0.76µm Gold (Au) Plating, without Pegs	2048430001
Mirror Mezz Hermaphroditic Connectors	203456
Mates With	This is a hermaphroditic, self-mating part.

Downloaded from Arrow.com.