

Product information

OVKS 2,2

Fiber Interfaces: Assimilable LWL components: OptoQuick components: OVKS 2,2

<https://e-catalog.beldensolutions.com:443/link/57078-57141-57136-24571-38339/en/conf/ui/state>

Name	
OVKS 2,2	
	
fiber optic plug; for plastic fiber with an external diameter of 2.2 mm, strain relief 40 N	
Delivery informations	
Availability	available
Product description	
Description	fiber optic plug; for plastic fiber with an external diameter of 2.2 mm, strain relief 40 N
Construction type	OVK OptoQuick
Colour	black
Type	OVKS 2,2
Order No.	936 200-001
Scope of delivery and accessories	
Scope of delivery	20 fiber optic plugs, each consisting of a plug body and a strain relief 1 polishing tool 1 operating instructions

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.