

## Technical data sheet

Article number:  
118-05040

**T50ROS**



<b>Product Group</b>	Cable ties for thin-walled bundles
<b>Product Family</b>	OS-Series
<b>Material</b>	Polyamide 6.6, heat stabilised (PA66HS)
<b>Colour</b>	Black (BK)
<b>Application Tool</b>	ProCut 9 no battery, MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7iSP, EVO9, EVO9SP, EVO9i, EVO9iSP
<b>Bundle Ø max.</b>	50.0 mm
<b>Bundle Ø min.</b>	1.6 mm
<b>Flammability</b>	UL 94 V2
<b>Halogen-free</b>	Yes
<b>Height (H)</b>	1.3 mm
<b>Length (L)</b>	200.0 mm
<b>Min.Tensile Strength</b>	225 N
<b>Operating Temperature</b>	-40 °C to +105 °C, (+145 °C, 500 h)
<b>Package Content packed in</b>	pcs.
<b>Pack Cont.</b>	500 pcs.
<b>Releasable Closure (Yes/No)</b>	No
<b>Thickness (T)</b>	1.3 mm
<b>Toothing (Serration)</b>	Outside Serrated
<b>Variant</b>	Outside Serrated
<b>Weight/Unit</b>	0.001263 kg
<b>Width (W)</b>	4.6 mm

