Part Number : 1121055006
Product Description : Direct-Link Industrial 8-Port, IP67 (Machine Mount) Ethernet Switch, Unmanaged, M12 Ultra-Lock, 10/100 Mb/s
Series Number : 112105
Status : Obsolete
Product Category : Industrial Ethernet Switches
Engineering Part Number : DRL-782

Obsolete

Documents and Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Obsolete
Category	Industrial Ethernet Switches
Series	112105
Description	Direct-Link Industrial 8-Port, IP67 (Machine Mount) Ethernet Switch, Unmanaged, M12 Ultra-Lock, 10/100 Mb/s
Approvals	CE certified, UL (pending)
Comments	2.4W (24VDC)
IP Rating	IP67
Product Name	Direct-Link
Protocol	EtherNet (IEEE 802.3)
Switch Functionality	Unmanaged
UPC	887191685229

Electrical

Current - Maximum Output	N/A
EMC	EN 61000-4-2, EN 61000-4-4, EN 61000-4-5, EN 61326
Supply Voltage	2.4W (24V DC)

Physical

Ethernet Connector	4-Pole Ultra-Lock (M12) Conn
Housing Width	60.00mm
MAC Address	N/A
Mechanical Shock	50G (IEC 68-2-29)
Mounting Style	N/A
Net Weight	1.000/g
Packaging Type	Carton
Ports	8
Power Input	5-pole Micro-Change (M12)
Temperature Range - Operating	-40° to +75°C
Uplink Connection	5-Pole Micro-Change (M12)
Vibration	7g (IEC 68-2-29)

Obsolete

Downloaded from Arrow.com.

This document was generated on May 16, 2026

Obsolete

Downloaded from Arrow.com.