



Part Number : [1301080199](#)
Product Description : Super-Safeway Wet Location
80W Fluorescent Tube Light with 2 Lamps, Cord Type
16/3 SOOW, Cord Length 7.62m (25.0')
Series Number : 130108
Status : Active
Product Category : Lamps and Lights
Engineering Number : 2030



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130108
Description	Super-Safeway Wet Location 80W Fluorescent Tube Light with 2 Lamps, Cord Type 16/3 SOOW, Cord Length 7.62m (25.0')
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Product Name	Super-Safeway
Type	Wide Area Lamps
UPC	78678867202

Agency

CSA	LR85374
UL	E174254

Electrical

Lamp Wattage - Maximum	80W
Lumens	6300
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Fluorescent
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SOOW
Depth	101.60mm (4.000")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	N/A

Lamp Type	PL-L 40/41
Length	955.55mm (37.620")
Material - Globe	Butyrate
Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Adjustable Brackets
Outlet	None
Packaging Type	Carton

This document was generated on Sep 16, 2025