



Part Number : [1301800314](#)
Product Description : MAX-LOC O-Ring, 1/2" NPT
Series Number : 130180
Status : Active
Product Category : Cable Grips
Engineering Part Number : 00-0820




Documents and Resources

Drawings

[1301800314_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Cable Grips
Series	130180
Description	MAX-LOC O-Ring, 1/2" NPT
Comments	Indicates that one or more grommet hole is covered by a thin membrane which can easily be "Poked" open if required.
Product Name	MAX-LOC
Type	O-Ring
UPC	78678802153

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	N/A
Color - Grommet	N/A
Eye Type	N/A
Gender	N/A
Material - Body	Neoprene
Material - Grip	N/A
Mesh Length	N/A
Net Weight	0.907/g
Number of Holes	1
O-Ring	Yes
Thread Size	1/2" NPT

Mates With / Use With

Use with Part(s)

Description	Part Number
Strain Relief Grips	<u>130096</u>
Strain Relief Grips	<u>130097</u>
MAX-LOC Strain Relief Grips	<u>130098</u>
MAX-LOC Strain Relief Grips and Accessories	<u>130099</u>

This document was generated on Dec 29, 2025