


Blind sleeve - CES-LTPG-GY - 0801716

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Large blind sleeve, material: SEBS



Product Description

Blind sleeves seal feed-through sections that are not required in CES sealing frames

RoHS

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 046356 675178
GTIN	4046356675178
Weight per Piece (excluding packing)	31.200 g
Custom tariff number	40169997
Country of origin	Poland

Technical data

Dimensions

Conductor sealing range	Blind sleeve
Length	29.5 mm
Width	19.5 mm
Height	17 mm

Ambient conditions

Degree of protection	IP54 (Observe the assembly instructions)
Ambient temperature (operation)	-40 °C ... 80 °C (static)

Blind sleeve - CES-LTPG-GY - 0801716

Technical data

General

Product description	Blind sleeves seal feed-through sections that are not required in CES sealing frames
No. of conductors	0
Material	SEBS
	SEBS (halogen-free)
Flammability rating according to UL 94	V0
Color	gray
Assembly note	IP54: for vertical sealing frame mounting/for horizontal sealing frame mounting (downward cable outlet direction).

Standards and Regulations


Connection in acc. with standard	CUL
----------------------------------	-----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Dimensional drawing



Dimensional drawing

Classifications

eCl@ss

eCl@ss 10.0.1	27144425
eCl@ss 11.0	27144425
eCl@ss 4.0	27081000
eCl@ss 4.1	27081000
eCl@ss 5.0	27081000
eCl@ss 5.1	27081000
eCl@ss 6.0	27081000

Blind sleeve - CES-LTPG-GY - 0801716

Classifications

eCl@ss

eCl@ss 7.0	27069220
eCl@ss 9.0	27144425

ETIM

ETIM 3.0	EC000879
ETIM 4.0	EC000451
ETIM 6.0	EC000451
ETIM 7.0	EC000451

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121448
UNSPSC 18.0	39121448
UNSPSC 19.0	39121448
UNSPSC 20.0	39121448
UNSPSC 21.0	39121448

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / DNV GL / cULus Recognized

Ex Approvals

Approval details

UL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

NITW2.E255026

Blind sleeve - CES-LTPG-GY - 0801716

Approvals

cUL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

NITW8.E255026

DNV GL



<https://approvalfinder.dnvgl.com/>

TAE00003VJ

cULus Recognized

