





NOTE
 SEAL TO BE PROVIDED BY USER

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH		THIRD ANGLE PROJECTION 
CHARACTERISTICS	ELECTRICAL DATA	SCALE 1/2 : 1
OPERATING POSITION-----1.125 MAX IN ANY DIRECTION	CONTACT ARRANGEMENT (SEE CIRCUIT DIAGRAM)	DO NOT SCALE PRINT
OPERATING FORCE-----5 OZ MAX	10A-120, 240 OR 480 VAC 1/3 HP-120 VAC; 3/4 HP-240 VAC 0.8A-115 VDC; 0.4A-230 VDC; 0.1A-550VDC PILOT DUTY 600 VAC MAX	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
FORCE AT 2.0-----10 OZ MAX		ONE PLACE (.0) ±.030
SWITCH-BASIC REPLACEMENT-----2MN1		TWO PLACE (.00) ±.015
		THREE PLACE (.000) ±.005
		ANGLES ±
		WEIGHT