





1	2
Connector Location A	


7	8
Connector Location B	



Loading-Plan:



- Protection level: IP 65/67
- Temperature range: -25°C ... +80°C



length in "1m" step	40	XXX=400
	39	XXX=390
	⋮	⋮
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	⋮	⋮
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	<u>XXX</u>

4.0 to 40	+1%
0.1 to 3.9	+0.04
a [m]	Tolerance

Part no.	213480833XXX
----------	--------------

Type of cable	XX
PVC grey, 3x0.25mm ²	XX=80
PUR black, 3x0.25mm ²	XX=88

		All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing 2016-09-06	
		All rights reserved Department HCS - RO		Created by MUNTEANV		Inspected by POPESCUD		Standardisation AVRAM	
HARTING Customised Solutions D-32427 Minden		Title M8 Cable Assembly		Date 2016-10-18		State Final Release		Doc-Key / ECM-Nr. 100578025/UGD/009/B 500000110271	
		Type TB		Number 213480833XXXXX		Rev. B		Page 1/1	