

nas1831c3a05

| | |
|----------------------|--|
| Brand | RAF |
| CAD Key | nas1831c3a05 |
| Finish | Passivated |
| Finish Description | Passivate (AMS2700), Method 1, Class 4 |
| Length | 0.3125 in |
| Material | Steel 303 |
| Material Description | Corrosion resistant steel (CRES) (ASTM A582/A582M), type 303 (UN S30330) or 303SE (UNS S30323) or XM-1 (UMS S20300), condition A |
| Model Number | NAS1831 |
| Outside Diameter | 0.1875 in |
| Thread Size | 2-56 |
| Thread Type | Female, Female |
| Brand | RAF |
| CAD Key | nas1831c3a05 |
| Finish | Passivated |
| Finish Description | Passivate (AMS2700), Method 1, Class 4 |
| Length | 7.94 mm |
| Material | Steel 303 |
| Material Description | Corrosion resistant steel (CRES) (ASTM A582/A582M), type 303 (UN S30330) or 303SE (UNS S30323) or XM-1 (UMS S20300), condition A |
| Model Number | NAS1831 |
| Outside Diameter | 4.76 mm |
| Thread Size | 2-56 |
| Thread Type | Female, Female |