



Color: ■ yellow Similar to illustration

Technical data	
Suitable	for wire cross-section 4 ... 6 mm²
Marking method	Thermal transfer
Delivery form	Roll
Delivery form configuration	20 m/roll
Printing device	Smart Printer (thermal transfer printer)

Physical data	
Depth	0.185 mm

Mechanical data	
Mounting type	Sliding on conductor
Shrink rate	2:1
Smear resistance	in conjunction with 258-5005 Ink Ribbon

Material data	
Color	yellow
Material	Polyolefin
UV resistance	EN 60068-2-5:2010 Procedure B
Adhesive information	without adhesive
Halogen-free	Yes
Weight	304.3 g
Fire load	0 MJ



Environmental requirements		
Ambient temperature (storage)		+10 ... +25 °C
Ambient temperature (operation)		-55 ... +125 °C
Relative humidity		45 ... 55 %

Commercial data		
PU (SPU)		1 pcs
Packaging type		Box
Country of origin		DK
GTIN		4055143370288
Customs tariff number		39173200900

Product classification		
UNSPSC		39121703
eCl@ss 10.0		27-40-04-01
eCl@ss 9.0		27-40-04-01
ETIM 9.0		EC001530
ETIM 8.0		EC001530
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant,No Exemption

Downloads		
Environmental Product Compliance		
Compliance Search		
Environmental Product Compliance		↓
211-503/000-002		

Documentation			
Operating Instructions			
211-502 Information on printing material	1	pdf	↓
	28.08.2020	1059.74 KB	