

**Part Number :** [1300950291](#)

**Product Description :** Multi-Weave Wire Mesh Pulling Grip, Flexible Eye, Mesh Length 1.321m (52.00"), Approximate Break Strength 11158.37kg (24600 lbs)

**Series Number :** 130095

**Status :** Obsolete

**Product Category :** Cable Grips

**Engineering Part Number :** 36643



---

## Documents and Resources

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

---

## Part Details

### General

Status	Obsolete
Category	Cable Grips
Series	130095
Description	Multi-Weave Wire Mesh Pulling Grip, Flexible Eye, Mesh Length 1.321m (52.00"), Approximate Break Strength 11158.37kg (24600 lbs)
Comments	Color Identifier Gold, Eye Cable Thickness 1/2"
Product Name	Multi-Weave
Type	Pulling Grip
UPC	78678836643

### Agency

CSA	LR32159
-----	---------

### Physical

Approximate Break Strength	11158.37kg (24600 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	25.40-31.50mm (1.000-1.240")
Color - Grommet	N/A
Eye Type	Flexible
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	1.321m (52.00")
Net Weight	1406.140/g
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A