

1888863-4 Product Details

 [Live Product Chat](#)

No Image Available

1888863-4

TE Part Number: 1888863-4

[Preliminary](#) [Add to Part List](#)

Serial ATA & Serial Attached SCSI

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- Receptacle/Shell Assembly
- Receptacle
- Number of Positions = 36
- 1 Ports
- PCB Mount Angle = Vertical

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Receptacle/Shell Assembly
- [Gender](#) = Receptacle
- [Number of Positions](#) = 36
- Number of Ports = 1
- [PCB Mount Angle](#) = Vertical
- Receptacle Configuration = Mini-SAS
- [PCB Mount Style](#) = Thru Hole
- [PCB Retention Feature](#) = Yes
- Keyed = Yes
- Proprietary Name = EVERCLEAR

Mechanical Attachment:

- Stackable = No

Termination Related Features:

- Key Type = Universal
- Termination (Solder) Post Length (mm [in]) = 2.80 [0.1102]

Body Related Features:

- PCB Retention Method = Retention Solder Tails

Contact Related Features:

- Contact Material = Phosphor Bronze
- [Contact Mating Area Plating Material](#) = Gold (30) over Nickel (50)

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- [High Temperature Housing](#) = Yes

Packaging Related Features:

- Packaging Method = Tube

Other:

- Brand = Tyco Electronics