

D

C

B

A


D

C


B

A

754 SERIES MAGNETIC CIRCUIT



C1 = 1000pF, 2kV CAPACITOR
R1-R4 = 75 OHMS, 1/16W RESISTORS



SUGGESTED PCB LAYOUT
(Component Side)

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN L. VARELA - DOCK5 17MAR2005		CHK D. FAROLE 17MAR2005		APVD D. FAROLE 17MAR2005		MODEL NAME MAGJACK GANG		DESC 1X6 754 10/100 TAB UP W/ LED		SIZE A1		CAGE CODE C=6610084		DRAWING NO		RESTRICTED TO	
DIMENSIONS: INCHES				TOLERANCES UNLESS OTHERWISE SPECIFIED:		0 PLC ± -		1 PLC ± -		2 PLC ± .010		3 PLC ± .005		4 PLC ± -		ANGLES ± -		APPLICATION SPEC		CUSTOMER DRAWING	
PRODUCT SPEC 108-2100				SCALE NTS		SHEET 2		OF 2		REV G											