



NC3FD-LX-HE

3 pole female receptacle, solder cups, velour-chromium housing, machined gold contacts

Exclusive version of standard DLX Series. Valuable velour chromium plating. Extra high temperature resistant insulator material.

Features & Benefits

- ✓ Extra high temperature resistant insulator material
- ✓ Flammability UL94V-0
- ✓ Machined female contacts
- ✓ Valuable velour chromium plating of shell
- ✓ All metal housing offers best overall RF protection and electromagnetic shielding
- ✓ New duplex ground contact for excellent contact integrity between chassis and cable connector
- ✓ Female contact incorporates a solder barrier to prevent solder running into the contact mating area
- ✓ Larger solder contacts for easier termination
- ✓ Optional connection to easily join pin 1 to chassis ground
- ✓ D-style housing provides installation compatibility with industry standard D mounting dimensions

Technical Information

Product	
Title	NC3FD-LX-HE
Connection Type	XLR
Gender	female

Electrical	
Capacitance between contacts	$\leq 4 \text{ pF}$
Contact resistance	$\leq 5 \text{ m}\Omega$
Dielectric strength	1,5 kVdc
Insulation resistance	$> 10 \text{ G}\Omega$ (initial)
Rated current per contact	16 A
Rated voltage	$< 50 \text{ V}$

Mechanical	
Insertion force	$\leq 20 \text{ N}$
Withdrawal force	$\leq 20 \text{ N}$
Lifetime	> 1000 mating cycles
Wiresize	max. 2.5 mm^2
Wiresize	max. 14 AWG
Wiring	Solder contacts
Locking device	Latch lock
Chassis shape	D

Material	
Contact plating	2 µm Au over 2 µm Ni
Contacts	Brass (CuZn35Pb2)
Insert	Polyphenylene Sulfide (PPS 40% GR)
Locking element	Steel Ck67
Locking element plating	Nickel
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Velour Chromium

Environmental	
Flammability	UL 94 V-0
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C