



T3212 AND T3224 THERMAL TRANSFER PRINTERS

T3212 and T3224 Thermal Transfer Printers

The T3212 and T3224 are robust 24-hour duty cycle industrial computer-driven 300 or 600 dpi thermal transfer printers. They have been specially designed to print on a wide range of TE Connectivity (TE) labels, cable markers, and identification marker sleeves. They have a full-color touch screen interface, with intuitive icon-based setting adjustments. Various preloaded tutorials answer commonly-asked questions without the unit having to connect to the internet. If however an internet connection is required for your application, this can be done wirelessly via a local Wi-Fi network, or via cable: the printers are equipped with USB, Ethernet and serial ports. Labels or ribbons can also be loaded quickly and easily. “Smart” print heads have built-in memory to facilitate the maintenance program. This includes the tracking of prints and the printing temperature.

T3212 and T3224 Thermal Transfer Printers

APPLICATIONS

- Office environment
- Industrial environment

FEATURES

- One heavy duty printer for all TE Identifications products, in 300 DPI or 600 DPI for ultra-sharp printing.
- Side loading of labels and ribbons results in a smaller system footprint.
- Intuitive, icon-based printer setting adjustments and integrated help videos.
- Multiple connectivity options (hard wire and WiFi).

BENEFIT STATEMENTS

- Print on the large range of materials, including heat-shrink sleeves, continuous tube, cable tags, panel label, high-temperature electronics labels or basic materials.
- Printer settings can be adjusted quickly and easily with an intuitive color touch screen.
- Numerous possibilities in terms of network connections. WiFi option increases flexibility for where the printer can be located at the customer's premises.

ELECTRICAL

- 100 to 240VAC - 50/60Hz, PFC

MATERIALS

- Plastic and Metal

PARTS LIST

BU information

Part Number	Description
1-2186500-1	T3212-PRINTER
1-2186501-1	T3212-SWARE-PRINTER
1-2186502-1	T3224-PRINTER
1-2186503-1	T3224-SWARE-PRINTER
1-2186504-1	T3212-PRINTER-PRINTHEAD-300DPI
1-2186505-1	T3200-PRINTER-DRIVE-ROLLER
1-2186506-1	T3224-PRINTER-PRINTHEAD-600DPI
1-2186507-1	T3200-PRINTER-LOGICBOARD
1-2186508-1	T3200-PRINTER-PSU
1-2186509-1	T3200-PRINTER-PERFORATOR
1-2186510-1	T3200-PRINTER-CUTTER
1-2186511-1	T3212-PRINTER-COVER
1-2186512-1	T3224-PRINTER-COVER
1-2186513-1	T3200-PRINTER-CONTROL-PANEL
1-2186514-1	T3200-PRINTER-CUTTER-COVER
1-2186515-1	T3200-PRINTER-LABEL-SENSOR
1-2186516-1	T3200-PRINTER-CUT/PERF-ADDAPTOR
1-2186518-1	T3200-PRINTER-PRINTHEAD-LEVER
1-2186519-1	T3200-PRINTER-MEDIA-OUTERFLANGE

te.com

© 2018 TE Connectivity. All Rights Reserved.

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

1-1773955-4 09/18 Tangence