


Protect It! 230V 6-Universal Outlet Surge Protector, 1.8M Cord, German/French Plug, 750 Joules

MODEL NUMBER: **SUPER6OMNID**



Highlights

- 6 universal outlets
- 1.8 m power cord with German/French plug
- 750 joule rating
- Lighted on/off switch with integrated circuit breaker

Package Includes

- SUPER6OMNI D AC surge suppressor
- Instruction manual and warranty information

Description

The Protect It!® SUPER6OMNI D offers economical AC surge suppression for full protection of 220-250V workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. The SUPER6OMNI D offers six universal outlets and a 1.8-meter AC line cord with German/French plug. Internal shutters offer additional safety. AC suppression rated at 750 joules shields equipment from surges and line noise. Lighted on/off switch with integrated circuit breaker provides power control over connected equipment. Right-angle outlets keep connected cords from blocking adjacent outlets. Attractive light gray high-impact housing.

Features

- Protect It!™ SUPER6OMNI D offers economical AC surge suppression
- 750 joules AC surge suppression shields equipment from surges and line noise
- 6 universal outlets protect computers and peripherals
- 1.8 m AC line cord with German/French plug
- Internal shutters provide additional safety
- Built-in power switch and 10 amp circuit breaker offers power control and overload protection over all outlets
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Attractive light gray high-impact housing with keyhole mounting tabs allow versatile placement options
- Right-angle outlets keep connected cords from blocking adjacent outlets

Specifications

OVERVIEW	
UPC Code	037332121141



Powering Business Worldwide

TRIPP LITE
SERIES

INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Voltage Compatibility (VAC)	220-250
Maximum Surge Amps	13500
Input Plug Type	German; French
Input Cord Details	VDE H05VV-F 1.0mm2
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) Universal outlets
Circuit Breaker (amps)	10
Overload Protection	10A resettable illuminated combo switch/circuit breaker
Outlet Orientation	right-angled
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
Switches	Two position power switch
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	750
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Black



Powering Business Worldwide

TRIPP LITE
SERIES

Housing Color	Light Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	219.5 mm
Outlets Measurement (Center to Center)	51mm
Receptacle Color	Gray
Shipping Dimensions (hwd / in.)	17.20 x 2.00 x 4.60
Shipping Dimensions (hwd / cm)	43.69 x 5.08 x 11.68
Shipping Weight (lbs.)	1.44
Shipping Weight (kg)	0.65
Unit Dimensions (hwd / in.)	1.750 x 16.000 x 2.500
Unit Dimensions (hwd / cm)	39.4 x 6.4 x 3.2
Unit Weight (lbs.)	1.0
Unit Weight (kg)	0.45
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 104°F (-15° to 40°C)
Operating Humidity Range	20% to 85% RH
Storage Humidity Range	0% to 90% RH
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.