Part Number : 1300250125
Product Description : Mini-Change A-Size Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 18/15 AWG, Gray DeviceNet Thick (Trunk) Cable, 60.0m (196.85') Length
Series Number : 130025
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : DN11A-M600



Documents and Resources

Drawings

1300250125_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead... per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	130025
Description	Mini-Change A-Size Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 18/15 AWG, Gray DeviceNet Thick (Trunk) Cable, 60.0m (196.85') Length
IP Rating	IP67
Product Name	DeviceNet Trunk,Mini-Change
Type	Double Ended
UPC	78678837191

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	300V AC/DC

Physical

Cable Diameter	12.10mm (.480")
Cable Length	60.0m (196.85')
Color - Cable Jacket	Gray
Connector End A	Mini-Change
Connector End B	Mini-Change
Coupling Style	Threaded

Downloaded from Arrow.com.

Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Zinc Die-Cast
Material - Plating Mating	Gold
Net Weight	854.250/g
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-20° to +60°C
Wire/Cable Type	Thick (Trunk)
Wire Size (AWG)	15, 18

Downloaded from Arrow.com.