



**Part Number :** [1301460147](#)

**Product Description :** Watertite Extreme Receptacle with Single Flip Coverplate with Locking Blade, 2 Pole/3 Wire, NEMA L7-15, 277V

**Series Number :** 130146

**Status :** Active

**Product Category :** Wiring Devices

**Engineering Part Number :** 65W34

---

## Documents and Resources

### Drawings

[1301460147\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)


[SOLIDWORKS](#)

[Creo](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

### [Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extreme Receptacle with Single Flip Coverplate with Locking Blade, 2 Pole/3 Wire, NEMA L7-15, 277V
IP Rating	IP67
NEMA Configuration	NEMA L7-15
Product Name	Watertite Extreme
Specialty	N/A
Type	Receptacle
UPC	78678871504

### Agency

CSA	LR6837
UL	E68122

### Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	277V

### Physical

Cord Type	N/A
Flange	No
Flip Lid	Yes
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes
Net Weight	44.110/g
Poles	2-pole/3-wire
Receptacle Type	Single

---

This document was generated on Apr 26, 2026