Datasheet for part number THV0U14-0400S1L-02

Our Descriptive Part Number: THV0U14-0400S1L-02
Our Global Manufacturing Part Number: 192993-0704
Brand: Cannon Product Category: Trident Product Line: Trident Series: THV

Product Datasheet	
Series	Trident High Voltage
Connector Type	Receptacle for Flange Mounting
Environmental Sealing	IP67
Sealing Methode	no sealing
Shell Size	14
Contact Quantity	4
Power Contacts	4
Signal Contacts	0
Contact Gender	Socket
Contacts included	No, order separately
Operating Voltage	Up to 500 V (dc and ac)
Current Rating	Up to 30 A
Operating Temperature	-40°C to +125°C (-40°F to +257°F)
Insulator Resistance	5000 Megaohms at 500 V dc
Durability	Up to 50 Mating Cycles
Flammability	UL94-V0
Salt Spray	48 hours
Vibration	10 g's peak, 10 to 500 Hz, 9 hours
Physical Shock	40 g's peak, 6msec., half-sine pulse
Insulator Material	Orange Nylon
Coupling Nut Material	Nickel Plated Brass
Shell Material	Nickel Plated Zinc Alloy
VDE Certified	VDE Reg.-Nr. D588

Specifications and dimensions subject to change.

Downloaded from Arrow.com.