

Part Number : [399800409](#)


Product Description : 5.08mm Pitch Beau Eurostyle Surface Mount Compatible Locking Header, 9 Circuits

Series Number : 39980

Status : Obsolete

Product Category : Terminal Blocks and Barrier Strip

Engineering Part Number : 981509



Documents and Resources

[399800409_stp.zip](#)

Specifications

[PS-39980-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Terminal Blocks and Barrier Strip
Series	39980
Description	5.08mm Pitch Beau Eurostyle Surface Mount Compatible Locking Header, 9 Circuits
Application	Wire-to-Board
Comments	Gold plating available
Component Type	PCB Header
Product Name	Eurostyle Pluggable
Type	PCB Terminal Blocks and Connectors
UPC	800756374765

Agency

UL	E48521
----	--------

Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	300V

Physical

Circuits (Loaded)	9
Color - Resin	Black
Entry Angle	N/A
Flammability	94V-0
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Plating Termination	Tin

Material - Resin	Nylon
Number of Rows	1
Orientation	Vertical
Panel Mount	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
PC Tail Length	3.81mm
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Plating min - Mating	3.810µm
Plating min - Termination	3.810µm
Polarized to Mating Part	Yes
Shrouded	No
Stackable	No
Temperature Range - Operating	140°C
Wire Size (AWG)	N/A

This document was generated on Dec 14, 2025

Obsoleted