Part Number : 1301370087
Product Description : Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, Cord Clamp, Duplex Cover Plates only
Series Number : 130137
Status : Active
Product Category : Power Distribution
Engineering Part Number : 3000



Documents and Resources

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power Distribution
Series	130137
Description	Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, Cord Clamp, Duplex Cover Plates only
Enclosure Rating	NEMA 4
NEMA Configuration	N/A
Product Name	Super-Safeway
Type	Multiple Outlet Box
UPC	78678875050

Agency

UL	E46237

Electrical

Current - Maximum per Contact	Per Cust. Supplied Receptacle
GFCI	No
GFCI Reset	N/A
Ground Continuity Monitor	No
Open Neutral Relay	N/A
Voltage - Maximum	Per Cust. Supplied Receptacle

Physical

Cord Diameter	8.26-16.64mm (.325-.655")
Cord Grip Body Size	F3 3/4"
Cord Length	N/A
Cord Type	N/A
Feed-Thru	No
Flip Lid	Yes

Downloaded from Arrow.com.

Material - Housing	Rubber
Mounting Style	Portable
Net Weight	420.026/g
Number of Receptacles	2 - Customer Supplied
Packaging Type	Carton
Receptacle Type	Duplex

Downloaded from Arrow.com.