
Part Number : 510050300
Series Number : 51005
Status : Active - Proprietary



Specifications

SPK-51005-001-001.pdf

PS-51005-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Active - Proprietary
Category	Connector Housings
Series	51005
Description	2.00mm Pitch Wire-to-Wire Receptacle Housing, 3 Circuits
Application	Wire-to-Wire
Component Type	Receptacle
Product Name	N/A
UPC	800753630239

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	3
Color - Resin	Natural
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	No
Material - Resin	Polyester
Net Weight	175.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number

Downloaded from Arrow.com.

2.00mm Pitch Wire-to-Wire Plug Housings	51006

Use with Part(s)

Description	Part Number
2.00mm Pitch Crimp Terminals	50013

Downloaded from Arrow.com.