

- Electromechanical Components
- > Connectors
- > Relays
- > Touch Panels
- > KVM Switches
- > Thermal Printers

> 24 Volt Mechanisms

> 24 Volt Kiosk Printers

> 5 Volt Kiosk Printers

> Battery Operated Mechanisms

> Mobile Printers

> Standalone Printers

> Interface Boards

> Input Devices

> Wireless Modules

> Optical Modules

> DC/DC Converters

KA02066-D105

RoHS compliant

Mechanism

Type24V

Status✔ Active

Size3"

CutterWith cutter

Paper InsertionTop

Datasheet PDF [KA02066-D105 \[1MB\]](#)

DescriptionStandalone printer. FP-1000 series. High-speed, 180mm/sec, compact design and small footprint. Dual interface (serial 25-pin and USB type-B). With AC adaptor, without AC cable. Black cover.


Notes [FP-1000 series](#)



We're Here to Help

- How to Buy
- [Sales contacts](#)
 - [Stock check](#)
- Support Info
- [Technical / sales support](#)

[Top of Page](#)

Services & Solutions	Products	Help and Support	Most Popular	Country Selector
Business Services	Computing Products	Support & Downloads	FUJITSU Image Scanner	United States Change <div></div>
Managed Infrastructure Services	Servers	Support for Fujitsu Scanners	Notebooks	
Fujitsu Retailing Solutions	Network Products	Notebooks & Tablet PCs	Store Technology	
Network Services	Semiconductors	Shop Fujitsu	PalmSecure®	
ASIC and Foundry Services	Components	How to Buy	UHF RFID Tag	