

**Part Number :** [936011754](#)

**Product Description :** Heavy-Duty Standard (STD) Double Lever Hood, Die-cast Aluminum, with 2 Levers, Top Entry, with Gasket, Size 24B «104x27», Extended M25 Thread, Grey

**Series Number :** 93601

**Status :** Active

**Product Category :** Heavy-Duty Connectors

**Engineering Part Number :** 7810.6586.0



---

## Documents and Resources


### Drawings

[936011754\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

## CE - Declaration of Conformity

## UKCA - Declaration of Conformity

---

## Part Details

### General

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty Standard (STD) Double Lever Hood, Die-cast Aluminum, with 2 Levers, Top Entry, with Gasket, Size 24B «104x27», Extended M25 Thread, Grey
Component Type	Double Lever Hood
IP Rating	IP66
Product Name	Heavy-Duty Connectors
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191846392

### Agency

CSA	256883
UL	E249674

### Electrical

Voltage - Maximum	500V
-------------------	------

### Physical

Component Size	10B «57X27»
Entry Location	Top

Hood Coating	Polyester Powder
Hood Color	GREY RAL 7037
Lock to Mating Part	Yes
Material - Gasket	NBR
Material - Hood	Die-cast Aluminum
Material - Lever	Galvanized Steel
Net Weight	185.000/g
Number of Levers	2
Packaging Type	Bag
Thread Size	M25
Thread Type	(M) Metric

## Mates With / Use With

### Use with Part(s)

Description	Part Number
Use With	Size 10B «57x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts

---

This document was generated on Apr 29, 2026