


Part Number : 1300940414

Product Description : Standard Duty Support Grip, Offset Eye, Split Rod, Single Weave, Cable Diameter 31.75-37.85mm (1.250-1.490"), Approximate Break Strength 762.04kg (1680 lbs)



Series Number : 130094

Status : Active

Product Category : Cable Grips

Engineering Number : 35304

Documents & Resources

Drawings

[PK-130227-004-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130094
Description	Standard Duty Support Grip, Offset Eye, Split Rod, Single Weave, Cable Diameter 31.75-37.85mm (1.250-1.490"), Approximate Break Strength 762.04kg (1680 lbs)
Product Name	Standard Duty
Type	Support Grip
UPC	78678835304

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	762.04kg (1680 lbs)
Bale Length	0.127m (5.00")
Body Style	Straight
Cable Diameter	31.75-37.85mm (1.250-1.490")
Color - Grommet	N/A
Eye Type	Offset
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.406m (16.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A

This document was generated on Sep 17, 2025