
Part Number : 1600744012
Product Description : MX150 Mat-Sealed Female Connector Assembly, Dual Row, 8 Circuits, UL 94V-0, Keying Option B, with Clipslot, without Connector Position Assurance, Light Gray
Series Number : 160074
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

1600744012_sd.pdf

PK-31300-635-001.pdf

PK-31300-903-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

AS-33472-100-001.pdf

AS-33472-100-CH-001.pdf

AS-33472-100-FR-001.pdf

AS-33611-001-001.pdf

PS-160074-0001-001.pdf

1600742276-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Dodecamethylcyclohexasiloxane;

Downloaded from Arrow.com.

	Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	160074
Description	MX150 Mat-Sealed Female Connector Assembly, Dual Row, 8 Circuits, UL 94V-0, Keying Option B, with Clipslot, without Connector Position Assurance, Light Gray
Application	Wire-to-Board, Wire-to-Wire, Automotive
Component Type	Receptacle
Product Name	MX150
UPC	191128118729

Agency

Downloaded from Arrow.com.

UL	E29179

Physical

Circuits (maximum)	8
Color - Resin	Gray (Light)
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	14.538/g
Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarization	B
Polarized to Mating Part	Yes
Sealed	Sealed
Stackable	No
Temperature Range - Operating	-40° to +125°C
Terminal Size	1.5

Mates With / Use With

Use with Part(s)

Description	Part Number
MX150 Sealed Receptacle Cavity Plug	343454001
MX150 Backshell for Female Sealed Connector Assembly, 8 Circuit, with Rib	349510811
MX150 Backshell for Female Sealed Connector Assembly, 8 Circuit, without Rib	349510821
MX150 90° Backshell Adapter for Female and Male Sealed	349510831

Downloaded from Arrow.com.

Connector Assembly, 8 Circuit, with Rib	
MX150 90° Backshell Adapter for Female and Male Sealed Connector Assembly, 8 Circuit, without Rib	349510841
MX150 Female Terminals	33001
MX150 Female Terminals	33012

Downloaded from Arrow.com.