

BPMI0004044065NL0K

Search by : Part Number Characteristics Cross reference



NEW


Closed Magnetic Circuit Type High Current & High Frequency

Series Pdf

Product detail	
L(mm) ±	4.0Max.
W(mm) ±	4.0Max.
T(mm) ±	4.0Max.
Inductance(uH)	0.065
Tolerance(±%)	15
Test Frequency	100kHz,1V
RDC(ohm)	0.32
RDC Tolerance(±%)	9
Isat(A)Typ	25
Irms(A)Typ	19
Operating Temperature	－40℃ ~ 125℃(Including self - temperature rise)

Part Numbering Dimensions Packing Recommended Pattern Electrical Characteristics

Downloaded from Arrow.com.



Products

Power Inductor

EMI-Common Mode Choke

EMI-Bead

RF-Signal Inductor

RF-Filter/Antennas

RF-Wireless Power Transfer

LAN Transformer

Resistor & Current Sensor

Applications

Automotive

Industrial

Server/DataCenter

Communication

Mobile and Tablet

Computer/Laptop

Consumer

Design Tools

Simulation Tool

Product Search Engine

E-Catalogue

About Us

Corporate Overview

Corporate Milestones

Core Technology

Certificates & Awards

Quality and Social Responsibility

Investor

Financial Information

Corporate governance

Stakeholder Contacts

Downloaded from Arrow.com.

News

Media Center

New Products

Events

Product Notices

Contact Us

Contact Info

Contact Form

Join Chilisin

Terms of Use

Privacy policy

Sitemap



Inductor Resistor Powder

Copyrights © 2018. Chilisin. All rights reserved.

Downloaded from Arrow.com.