






FRONT VIEW



SIDE VIEW



RECOMMENDED P.C.B. LAYOUT  
(COMPONENT SIDE OF BOARD)

DATA CONTROL  
RELEASE

DEPT. NO.--626--  
DATE: JUN 30, 2009

1. MATERIALS:

PLASTIC HOUSING: ENGINEERING THERMOPLASTIC  
FLAMMABILITY RATING UL 94V-0  
COLOR: PANTONE GREEN 362C

CONTACTS:

PHOSPHOR BRONZE  
PLATING: REFER TO PART NUMBER FOR GOLD  
THICKNESS ON MATING SURFACES.  
50  $\mu$ " [1.27 MICRONS]  
MIN. NICKEL UNDERPLATE  
100  $\mu$ " [2.54 MICRONS]  
MIN. MATTE TIN OR GOLD FLASH  
ON CONTACT TAILS.

PART NUMBER: RJE08-188-0XA0

GOLD PLATING:

- 1 = 6  $\mu$ "
- 2 = 15  $\mu$ "
- 3 = 30  $\mu$ "
- 4 = 50  $\mu$ "

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION  
MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING  
PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

|                   |              |      |            |
|-------------------|--------------|------|------------|
| DRAWN             | Huilan W     | DATE | MAY 11, 09 |
| DESIGNED          | MT Chen      | DATE | MAY 11, 09 |
| CHECKED           | L.Chan       | DATE | MAY 11, 09 |
| I. E. APPRD.      |              |      |            |
| Q. A. APPRD.      |              |      |            |
| DWG. APPRD.       |              |      |            |
| ENG. REL. NO.     |              |      |            |
| REF.              |              |      |            |
| DIMENSIONS ARE IN | CODE ID. NO. |      |            |
| INCHES [mm]       | 03554        |      |            |

Amphenol Canada Corp.

TITLE  
MODULAR JACK, TOP ENTRY,  
8 POSITION, 8 CONTACTS, WITH FLANGE,  
UNSHIELDED, - RoHS COMPLIANT

DWG DRAWING NO. P-RJE08-188-0XA0 REV. C

SCALE WT. SURF. SHEET 1 OF 1