



Part Number : [1300340007](#)
Product Description : Micro-Change (M12) Drop Connector, Threaded, Single Keyway, Straight Female, 5 Poles
Series Number : 130034
Status : Active
Product Category : Industrial Connectors
Engineering Part Number : 8A5000-32DN

Documents and Resources

Drawings
[1300340007_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Industrial Connectors
Series	130034
Description	Micro-Change (M12) Drop Connector, Threaded, Single Keyway, Straight Female, 5 Poles
Approvals	cCSAus certified
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Field Attachable Connector
UPC	78172553531

Agency

CSA	LR6837
-----	--------

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	36V

Physical

Cable Diameter	4.06-8.13mm (.160-.320")
Coupling Type	Internal Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	Single
Material - Connector Body	Polyamide
Material - Contact	Copper Alloy

Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	N/A
Net Weight	168.000/g
Orientation	Straight
Poles	5
Temperature Range - Operating	-25° to +90°C
Wire Size (AWG)	N/A

This document was generated on Aug 04, 2026