

CUSTOMER PRINT





PART NUMBER: W8380-XSG-P-5XX

- NOTES:
1. ALL PARTS TO BE BULK PACKED.
 2. CONTACTS SHIPPED UNASSEMBLED
 3. DIMENSIONS ARE REFERENCE EXCEPT THOSE WITH A TOLERANCE

ASS'Y P/N	CABLE O.D.
W8380-XSG-P-513	.13-.15 [3.3-3.8]
W8380-XSG-P-516	.16-.18 [4.1-4.6]
W8380-XSG-P-519	.19-.21 [4.8-5.3]
W8380-XSG-P-522	.22-.25 [5.6-6.3]
W8380-XSG-P-526	.25-.27 [6.4-6.9]
W8380-XSG-P-528	.26-.285 [6.6-7.2]

ASSEMBLY P/N	CONTACT QTY
W8380-2SG-P-5XX	2 #16
W8380-3SG-P-5XX	3 #16
W8380-4SG-P-5XX	4 #16
W8380-XSG-P-5XX	

GROMMET SIZE
NUMBER OF CONTACTS



DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS

CUSTOMER APPROVAL	
THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.	
APPROVED BY:	_____
DATE:	_____

RoHS COMPLIANT

A	MA	07-14-20	RELEASED PER PDR 16014-0	
	PNK	01-15-18	PDR 16014	
REV.	INIT.	DATE	DESCRIPTION	
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			ORIG. DRAWN BY: PNK	DATE: 01-15-18
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS. UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.010 ANGLES ±1° FRACTIONS ±1/16 = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			CHECKED BY:	 601 E. WILDWOOD VILLA PARK, IL 60181
APPROVED BY:			APPROVED BY:	
TITLE: CABLE-TO-CABLE CONNECTOR 2-4 #16 SOCKET CONTACTS, CRIMP INSTA-CLICK™ MINI-CON-X			SCALE: NTS	
FILE: W8380-XSG-P-5XX			SIZE: B	SHEET 1 OF 1
DIRECTORY: SLW			PART NUMBER: W8380-XSG-P-5XX	
CUSTOMER: STANDARD PRODUCT			REV A	